

Singapore | Malaysia | Sri Lanka | Philippines



Deblister RX-2™

Press -Out Semi Automatic Deblistering Machine

For recovering tablets and capsules from push-thru blisters



The Press-Out Semi Automatic deblistering machine is one of the latest additions to the Accuchart catalog. The machine belongs to the Press-Out Manual family. In addition to all the benefits of the Press-Out Manual Wide, it also has the following advantages:

- Empties up to 40 blister packs per minute

- Driven by a single phase electrical motor which runs continuously when packs are fed
- Can deblister packs with a diagonal/offset layout up to 170mm wide

- Integrated safety features such as a blister pack feed sensor which activates the roller mechanism only when a pack is placed over it

- Very flexible between different types of blister packs
- Fully cGMP and easily cleaned
- Handles PVC/ALU as well as ALU/ALU blisters
- Easy to use with no special skills required

The Press-Out Semi Automatic has only one adjustable set of change parts and can be set up for almost any blister pack up to 170mm wide. It is ideal for small batches and saves the fingers and joints by replacing hand deblistering. With very little practice 40 packs per minute can be recovered cleanly and hygienically.



info@omnihealthtech.com www.omnihealth.com.sg

Singapore 71 Tannery Lane #04-03 City Industrial Building Singapore 347807 Malaysia 13-01 Block A Tropicana Avenue 12 Persiaran Tropicana Tropicana Golf & Country Resort Jalan PJU 3, 47410 Petaling Jaya Selangor Darul Ehsan Malaysia Sri Lanka 38/20 Rukmani Devi Mawatha Negombo Sri Lanka Philippines L-324 One Oasis Hub Commercial Brgy. Santa Lucia Ortigas Ext. Pasig City Philippines 1608